


ASSEMBLY & OPERATING INSTRUCTIONS

MOTORIZED SHOE CLEANER MODEL #1600VA / #1600SA

- INSERT THE HANDLE INTO MATING SOCKETS IN THE SHOE BRUSH COVER. FOR PROPER INSTALLATION, THE HANDLE SHOULD BE INSERTED THE FULL DEPTH OF THE STUBS.



- TO OPERATE THE SHOE CLEANER, PUSH THE HANDLE SLOWLY FORWARD WHILE MOVING YOUR SHOE PLACED FLAT, AND IN A FORWARD MOTION BETWEEN THE ROTATING BRUSHES.

- NO INTERNAL CONNECTIONS OR ADJUSTMENTS ARE REQUIRED.

UCP

ULTRA-CLEAN PRODUCTS, L.L.C.

17882 SAMPSON LANE UNIT "C", HUNTINGTON BEACH CA 92627
PHONE (714) 596-3394 FAX (714) 375-9495
E-MAIL ultracleanprdts@aol.com

SPECIFICATION SHEET

MODEL# 1600-120V

SIZE OF MAIN UNIT.....18"W x 27"L x 10.5'H
WEIGHT.....50 LBS
SHIPPING WEIGHT.....58 LBS
VOLTAGE.....110 - 120V AC
CYCLE..... 60 CYL
AMPERAGE12 AMPS
ELECTRICAL CONNECTION.....Standard 110 – 120V Plug
VACUUM EXHAUST.....1.50 I.D. x 1.75 O.D.

U C P

ULTRA CLEAN PRODUCTS LLC

17882 SAMPSON LANE UNIT C. HUNTINGTON BEACH, CA 92647

PHONE 714 596-3394 FAX 714 375-9495

E-MAIL ULTRACLEANPRDTS@AOL.COM

MAINTENANCE SCHEDULE

ULTRA-CLEAN MOTORIZED SHOE CLEANER

MODEL # 1600

- THE MODEL 1600 MECHANICAL SHOE BRUSHER IS DESIGNED WITH VERY FEW MOVING PARTS AND REQUIRES MINIMAL MAINTENANCE.
- ALL MOTORS AND DRIVE COMPONENTS ARE FACTORY LUBRICATED FOR THE LIFE OF THE EQUIPMENT.
- THE FOLLOWING SIMPLE MAINTENANCE SCHEDULE SHOULD BE FOLLOWED BUT MAY VARY DEPENDING UPON USAGE.

EVERY TWO WEEKS

1. DISPOSABLE DUST BAGS SHOULD BE REPLACED (MODEL 1600VA ONLY)
2. UNIT SHOULD BE GENERALLY DUSTED AND CLEANED INSIDE.

ONCE A MONTH

1. VACUUM FILTER SHOULD BE REPLACED (MODEL 1600VA ONLY)
2. BRUSHES SHOULD BE INSPECTED AND REPLACED IF WORN TO ASSURE PROPER CLEANING ACTION.

NOTE:

TO PREVENT SCRATCHES CARE SHOULD BE TAKEN WHEN OPENING THE MACHINES COVER, AS IT RESTS ON THE FLOOR.

UCP

ULTRA-CLEAN PRODUCTS, L.L.C.

17882 SAMPSON LANE UNIT C, HUNTINGTON BEACH CA 926247

PHONE 714 596-3394 FAX 714 375-9495

E-MAIL ULTRACLEANPRDTS@AOL.COM

WARRANTY

ULTRA-CLEAN MOTORIZED SHOE CLEANER

MODEL # 1600-VA/1600-SA

● THE EQUIPMENT AS DESCRIBED ABOVE IS WARRANTED AGAINST DEFECTS, WORKMANSHIP AND MATERIAL FOR ONE YEAR FROM THE DATE OF SHIPMENT, PROVIDED THE RECOMMENDED MAINTENANCE SCHEDULE IS FOLLOWED AND THE MACHINE IS USED FOR THE PURPOSES FOR WHICH IT WAS INTENDED.

● IF IT IS DETERMINED THAT THERE IS A DEFECT IN WORKMANSHIP AND/OR MATERIAL WITHIN THE WARRANTY PERIOD, ULTRA CLEAN PRODUCTS INC. WILL REPAIR OR REPLACE THE DEFECTIVE PART OF PARTS (EXCEPT FOR THE BRUSHES AND VACUUM FILTERS) FREE OF CHARGE (EXCEPT FOR TRANSPORTATION CHARGES) WHEN RETURNED TO THE FACTORY.

WE ARE NOT LIABLE FOR CONSEQUENTIAL DAMAGES

● ALSO THIS STANDARD 1 YEAR WARRANTY IS INVALIDATED IF IT IS USED FOR ANY PURPOSE OTHER THAN WORKERS ENTERING THE "CLEAN ROOM TYPE AREA" WITH STANDARD STREET TYPE SHOES. ALSO THIS WARRANTY IS INVALIDATED IF USED BY CONSTRUCTION WORKERS WITH HEAVY DUTY TYPE CONSTRUCTION WORKERS FOOT WARE.

UCP

ULTRA-CLEAN PRODUCTS, L.L.C.

17882 SAMPSON LANE UNIT C, HUNTINGTON BEACH CA 926247

PHONE 714 596-3394 FAX 714 375-9495

E-MAIL ULTRACLEANPRDTS@AOL.COM